



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P2802-31M Lynzie

Lynzie Collection Two-Light Matte Black Etched Opal Glass Modern Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Oval



Width: 14.5 in
 Extends: 5-5/8 in
 Height: 11-1/8 in
 H/CTR: 8-5/8 in (glass facing up)

Etched Opal Glass Oval
 Width: 5-3/16 in
 Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	