

DATE:	TYPE:	
NAME:		
PROJECT:		



Incandescent

## P2997-163

## **Archie**

Opt for stronger focused light illumination with the impressive Archie four-light bath. Four refined, double-prismatic glass shades hang shoulder to shoulder, each supported by its own curved arm. A single, straight bar supports the light sources and fuses the entire structure to a circular backplate. With its Vintage Brass finish, the fixture is perfect for inspiring an old-world feel as it brightens a bathroom or dressing table mirror, a hallway, or wherever focused light is called upon in farmhouse and transitional interiors.

- Perfect for above a bathroom or dressing table mirror, in a hallway or wherever focused light is desired
- Distinctive, double-prismatic glass shades adds visual texture while providing functional illumination
- The cross-patterned, prismatic glass shades combined with vintage metal detailing offer an ideal look for farmhouse and transitional settings
- Four-light bath vanity with strap and vintage knob detailing
- Finished in beautifully muted Vintage Brass
- Can be mounted facing up or down and includes installation instructions and mounting hardware
- Measures 35-1/2 in width X 8-3/4 in height, Extends 7 in, H/CTR 5-1/4 in
- Uses four 100-watt max medium base bulbs, or the LED equivalents, that are sold separately
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction

Glass/Shade: Clear double prismatic glass shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	UL/CUL Damp location listed
Mounting strap for outlet box included  Fixture can be installed with glass	6" of wire supplied 120 V	Four 100w max. Medium Base E26 base ceramic sockets	1 year warranty
facing up or down			
Back plate covers a standard 4" octagonal recessed outlet box			
5.125" W., 1" ht., 5.125" depth			

H/CTR: 5-1/4" (glass facing up)

Glass

Width: 5-3/4" Length: 5-3/4" Height: 4-5/16"