

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300029-143

Gauge

Inspired by industrial elements, Gauge two-light bath features an open cage design that's both functional and aesthetically appealing. Frame is comprised of a Graphite finished wire frame with Brushed Nickel accents. Hinged door provides easy access to change lamp.

- Graphite finish with Brushed Nickel accents
- Industrial inspired design
- Features an open cage with hinged door
- Shown with Vintage lamps (P7825-01)
- Brushed Nickel accents

Category: Bath & Vanity

Finish: Graphite (painted)

Construction: Steel construction



Width: 15-5/8"
Height: 11"
Depth: 7-1/4"
H/CTR: 3" (facing up)

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|--|--|--|
| <p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Fixture can be installed with glass facing up or down</p> <p>Backplate covers a standard 4" hexagonal recessed outlet box, 6" W., 6" ht., 0.75" depth</p> | <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p> | <p>Quantity:</p> <p>Two 60w max. Medium Base E26 base ceramic socket</p> | <p>cULus Damp location listed</p> <p>1 year warranty</p> |