

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P300039-009**  
**Bramlett**

Bramlett Collection One-Light Brushed Nickel Graphite Metal Shade Coastal Bath Vanity Light

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Graphite Metal Shade



Width: 6 in  
Height: 8-1/8 in  
Depth: 7-1/8 in  
H/CTR: 4-1/2 in (glass facing up)

Graphite Metal Shade  
Width: 6-1/16 in  
Height: 6-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	(1) Medium Base (E26) socket	cULus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
back plate covers a standard 4" recessed outlet box: 4.5" W., 7.0625" ht., 0.8125" depth		Fully dimmable with dimmable bulbs.	