## PROGRESS LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:



Calhoun Collection Three-Light Vintage Brass Clear Glass Farmhouse Bath Vanity Light

Category: Bath & Vanity Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Length: 21-5/8 in Extends: 6-7/8 in Height: 8-5/8 in H/CTR: 6-3/8 in (glass facing up)

Clear Glass Cylindrical Width: 4-11/16 in Height: 6-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 21.12" W., 4.5" ht., 0.62" depth		Fully dimmable with dimmable bulbs	