

Project:			
Fixture Type:			
Location:			
Contact			

## P300049-163 Hansford

Hansford Collection One-Light Vintage Brass Clear Glass Farmhouse Bath Vanity Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Round



Length: 6-1/2 in Extends: 7-1/4 in Height: 9-1/2 in

H/CTR: 6-7/8 (glass facing up)

Clear Glass Round Width: 6-1/2 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	CULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 5.12" ht., 0.81" depth		Fully dimmable with dimmable bulbs	