

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300051-104

Hansford

The Hansford collection of fixtures feature a clear, spherical shade paired with vintage style metal fittings in an antique bronze and brass combination finish. Featuring a clean and precise design with generous scale, Hansford's classic style brings tranquility to your home with. Hansford lends itself to Farmhouse, Coastal or Industrial interiors. Can be used with clear or vintage bulbs for a variety of looks. The three-light bath & vanity fixture can be mounted up or down.

- Hansford features a clear, spherical shade.
- Shade has a pleasing familiarity paired with vintage style metal fittings
- Features elegance and simplicity of nostalgic styles
- Polished Nickel finish.
- Fixture can be installed with glass facing up or down.

Category: Bath & Vanity

Finish: Polished Nickel (plated)

Construction: Steel Construction

Glass/Shade: Clear glass spherical shade



Width: 24-1/2"
Height: 10-7/8"
Depth: 7-1/4"
H/CTR: 8-1/4" (glass facing up)

Glass

Width: 6-1/2"

Height: 5-13/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 5.125" W., 5.125" ht., 0.8125" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Three 100w max. Medium Base E26 base socket	cULus Damp location listed 1 year warranty