

Project:		
Fixture Type:		
Location:		
Contact:		



## P300051-163

## Hansford

Hansford Collection Three-Light Vintage Brass Clear Glass Farmhouse Bath Vanity Light

Category: Bath & Vanity Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Round

Length: 24-1/2 in Extends: 7-1/4 in Height: 10-7/8 in

H/CTR: 8-1/4 in (glass facing up)

Clear Glass Round Width: 6-1/2 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 5.12" W., 5.12" ht., 0.81" depth		bulbs	