

Project:		
Fixture Type:		
Location:		
Contact:		



## P300052-163

## Hansford

 $\mbox{Hansford Collection Four-Light Vintage Brass Clear Glass Farmhouse Bath Vanity Light} \label{eq:light-light}$ 

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Round

Length: 33-1/2 in Extends: 7-1/4 in Height: 10-7/8 in

H/CTR: 8-1/4 in (glass facing up)

Clear Glass Round Width: 6-1/2 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 5.12" W., 5.12" ht., 0.81" depth	Fully dimmable with dimmable bulbs		