

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300068-020 Barnes Mill

Rustic and vintage decor can transform your home into a nostalgic retreat reminiscent of rural farmhouses. Exposed iron details and a faux-painted wooden plank support artful, clear, seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room. Four-Light bath & vanity fixture.

- Rustic and vintage lighting that transforms a home into a nostalgic retreat.
- A faux-painted wooden plank support artful, clear, seeded glass shades
- Design reminiscent of rural farmhouses
- Exposed iron details.
- Antique Bronze finish with faux wood painted bar.
- Combine with vintage-style light bulbs to create a romantic focal point to any room
- Fixture can be installed with glass facing up or down.

**Category:** Bath & Vanity

**Finish:** Antique Bronze (painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear Seeded glass shades



Width: 24 in  
Height: 8 in  
Depth: 5-7/8 in  
H/CTR: 5-3/4 in (glass facing up)

Clear Seeded glass shades  
Width: 3-15/16 in  
Height: 6-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Three 100 W max. Medium Base or LED equivalent	CULus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	E26 base socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V		
Back plate covers a standard 4" recessed outlet box: 8.0625" W., 4.5" ht., 0.8125" depth			