

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300105-009 Glayse

Inspired by modern architecture. Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function. One-Light bath & vanity is complimented by a Antique Bronze finish.

- Inspired by modern architecture
- Glayse features handsome details for variety of interior design styles - including mid-century modern, luxe, transitional and modern
- Popular Brushed Nickel finish
- The frameless unbounded beveled glass creates beautiful light and reflection
- Uses one 60-watt max. medium base bulbs including LED equivalent (sold separately)
- Perfect showcase for vintage style light bulbs, including Progress Lighting's P7825-01 or P7827-01
- The structure of Glayse is the focal point of the design, where form follows function
- Shop the complete Glayse collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor
- In addition to bath areas, sconces are suitable for hall & foyers to add ambient lighting
- Adds task lighting on either side of mirror to eliminate shadows on face when getting ready in the morning.

**Category:** Bath & Vanity

**Finish:** Brushed Nickel (plated)

**Construction:** Steel Construction

**Glass/Shade:** Clear glass Beveled Panel



Width: 7 in  
Height: 8-3/8 in  
Depth: 5-1/2 in  
H/CTR: 5-3/8 in (glass facing up)

Clear glass Beveled Panel

Width: 7 in  
Height: 6-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: One 60 W max. Medium Base or LED equivalent	CULus Damp Location Listed
Mounting strap for outlet box included	120 V	E26 base	1-year Limited Warranty
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 7" W., 6.75" ht., 7" depth			