

DATE:

NAME:

PROJECT:

Incandescent

P300120-009

TYPE:

Kene

Add a modern romance to the heart of your home with this lovely wall bracket. A quiet etched glass diffuser is surrounded by a clear outer shade for a soft, luxurious touch. The shades sit on an elegant brushed nickel frame with a rectangular backplate.

- A quiet etched glass diffuser is surrounded by a clear outer shade for a soft, luxurious touch.
- The shades sit on an elegant brushed nickel frame with a rectangular backplate.
- Add a modern romance to the heart of your home with this lovely wall bracket.
- Ideal for any bathroom.
- Perfect for modern, Craftsman, or contemporary settings.
- Measures 4-3/4-inch width by 12-7/8-inch height.
- Uses one medium base bulb that is sold separately (75w max LED, CFL, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity

Finish: Brushed Nickel (Plated)

Construction: Steel ConstructionGlass/Shade: Clear and Etched Glass Cylindrical Glass Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	cULus Damp location listed
Mounting Backplate for outlet box included	6" of wire supplied	One 75w max. Medium Base or LED equivalent	1-year Limited Warranty
Back Plate covers a standard 4" octagonal recessed outlet box		E26 base Porcelain socket	
Back Plate: 4.5" W., 7.875" ht., 0.75" depth			

Width: 4-3/4" Height: 12-7/8" Depth: 6-1/2" H/CTR: 8-7/8"

Glass Width: 4-3/4" Height: 5-9/16" Glass 2 Width: 2-15/16" Length: 2-15/16" Height: 4-3/4"