

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300121-009

Kene

Add a modern romance to the heart of your home with this lovely wall bracket. Quiet etched glass diffusers are surrounded by clear outer shades for a soft, luxurious touch. The shades sit on an elegant brushed nickel frame with a rectangular backplate.

- Quiet etched glass diffusers are surrounded by clear outer shades for a soft, luxurious touch.
- The shades sit on an elegant brushed nickel frame with a rectangular backplate.
- Add a modern romance to the heart of your home with this lovely wall bracket.
- Ideal for any bathroom.
- Perfect for modern, Craftsman, or contemporary settings.
- Measures 16-1/4-inch width by 7-3/8-inch height.
- Uses two medium base bulbs that are sold separately (75w max - LED, CFL, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity

Finish: Brushed Nickel (Plated)

Construction: Steel Construction **Glass/Shade:** Clear and Etched Glass Cylindrical Glass Cylindrical



Width: 16-1/4"
Height: 7-3/8"
Depth: 7-1/4"
H/CTR: 4-5/8" (glass facing up)

Glass

Width: 4-3/4"

Height: 5-9/16"

Glass 2

Width: 2-15/16"

Length: 2-15/16"

Height: 4-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting Backplate for outlet box included</p> <p>Fixture can be installed with glass facing up or down</p> <p>Back Plate covers a standard 4" octagonal recessed outlet box</p> <p>Back Plate: 7.875" W., 4.5" ht., 0.75" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Two 75w max. Medium Base or LED equivalent</p> <p>E26 base Porcelain sockets</p>	<p>cULus Damp location listed</p> <p>1-year Limited Warranty</p>