

DATE:	TYPE:	
NAME:		
PROJECT:		



Incandescent

P300122-143

Kene

Add a modern romance to the heart of your home with this lovely wall bracket. Quiet etched glass diffusers are surrounded by clear outer shades for a soft, luxurious touch. The shades sit on an elegant graphite frame with a rectangular backplate.

- Quiet etched glass diffusers are surrounded by clear outer shades for a soft, luxurious touch.
- The shades sit on an elegant graphite frame with a rectangular backplate.
- Add a modern romance to the heart of your home with this lovely wall bracket.
- Ideal for any bathroom.
- Perfect for modern, Craftsman, or contemporary settings.
- Measures 23-3/8-inch width by 7-3/8-inch height.
- Uses three medium base bulbs that are sold separately (75w max LED, CFL, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Width: 23-3/8" Height: 7-3/8" Depth: 7-7/8"

H/CTR: 4-5/8" (glass facing up)

Glass

Width: 4-3/4" Height: 5-9/16" Glass 2

Width: 2-15/16" Length: 2-15/16" Height: 4-3/4"

Category: Bath & Vanity
Finish: Graphite (Painted)

Construction: Steel ConstructionGlass/Shade: Clear and Etched Glass Cylindrical Glass Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting Backplate for outlet box included Fixture can be installed with glass facing up or down Back Plate covers a standard 4" octagonal recessed outlet box Back Plate: 7.875" W., 4.5" ht., 0.75" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Three 75w max. Medium Base or LED equivalent E26 base Porcelain sockets	cULus Damp location listed 1-year Limited Warranty