

DATE:	TYPE:	
NAME:		
PROJECT:		



Incandescent

P300123-009

Kene

Add a modern romance to the heart of your home with this lovely wall bracket. Quiet etched glass diffusers are surrounded by clear outer shades for a soft, luxurious touch. The shades sit on an elegant brushed nickel frame with a rectangular backplate.

- Quiet etched glass diffusers are surrounded by clear outer shades for a soft, luxurious touch.
- The shades sit on an elegant brushed nickel frame with a rectangular backplate.
- Add a modern romance to the heart of your home with this lovely wall bracket.
- Ideal for any bathroom.

Category: Bath & Vanity

- Perfect for modern, Craftsman, or contemporary settings.
- Measures 30-3/4-inch width by 7-3/8-inch height.
- Uses four medium base bulbs that are sold separately (75w max LED, CFL, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Width: 30-3/4" Height: 7-3/8" Depth: 8-1/8"

H/CTR: 4-5/8" (glass facing up)

Glass

Width: 4-3/4" Height: 5-9/16" Glass 2 Width: 2-15/16"

Length: 2-15/16" Height: 4-3/4"

Finish: Brushed Nickel (Plated)

Construction: Steel Construction Glass/Shade : Clear and Etched Glass Cylindrical Glass Cylindrical	

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting Backplate for outlet box included	Pre-wired 6" of wire supplied 120 V	Quantity: Four 75w max. Medium Base or LED equivalent	cULus Damp location listed 1-year Limited Warranty
Fixture can be installed with glass facing up or down Back Plate covers a standard 4" octagonal recessed outlet box		E26 base Porcelain sockets	
Back Plate: 7.875" W., 4.5" ht., 0.75" depth			