

DATE:	TYPE:	
NAME:		
PROJECT:		



Incandescent

P300125-141

Gulliver

The Gulliver Collection three-light bath & vanity feature a dual toned frame color combinations of Galvanized with antique white accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.

- Design complements Rustic and Modern Farmhouse home decor accents, as well as Urban Industrial and Coastal interior settings
- Metal banding features embossed wood grain pattern for rich visual texture
- Galvanized finish with hand painted antique white accents
- Dual-toned frame emulates popular design style that contains mixed metal accents
- Uses three 60 watt max, medium base lamps bulbs (sold separately)
- Shop the complete Gulliver collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor
- Adds task lighting on either side or above of mirror to eliminate shadows on face when getting ready in the morning
- In addition to bath areas, sconces are suitable for hall & foyers to add ambient lighting.

Category: Bath & Vanity

Finish: Galvanized Finish (painted)

Construction: Steel Construction

Glass/Shade: Clear Seeded Glass shade

Width: 24" Height: 8-1/2" Depth: 5"

H/CTR: 6-1/8" (glass facing up)

Glass

Width: 3-7/8" Height: 6"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6" of wire supplied	Quantity:	cETLus Damp location listed
Mounting strap for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 6.625" W., 4.75" ht., 0.75" depth	120 V	Three 60w max. Medium Base E26 base	1 year limited warranty