

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P300134-009

Leap

Leap vanity fixtures feature tapered etched glass shades to complement contemporary design trends.

- Design complements contemporary home accents for transitional and modern interiors
- Available in Brushed Nickel finish
- Features tapered etched glass shades
- Uses four 100 watt max, medium base lamps bulbs
- Fixture mounts up or down to suit preference
- Shop different sizes for Leap bath and vanity fixtures
- Adds task lighting on either side – or above – of mirror to eliminate shadows on face when getting ready in the morning.

Width: 31-3/4"
Height: 8-3/8"
Depth: 6-1/8"
H/CTR: 6" (glass facing up)

Glass
 Width: 5"
 Height: 6-3/8"

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass/Shade: Etched Glass shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 4.75" W., 7.875" ht., 0.875" depth	6" of wire supplied 120 V	Quantity: Four 100w max. Medium Base E26 base	cCSAus Damp location listed 1 year limited warranty