



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P300136-135

Union Square

Inspired by historical reproduction gas lanterns, Union Square now offers options in bath and vanity fixtures. A Stainless Steel finish complements the natural polished material and clear flat glass panels. The sconces are open on the top and bottom, providing character and visual appeal to the form.

Width: 30"
Height: 4-1/2"
Depth: 5"
H/CTR: 2-1/4"

- Design inspired by historical reproduction gas lanterns
- Features popular Stainless Steel finish to complement the natural polished material and clear flat glass panels
- Uses four 60 watt max, medium base lamps bulbs (sold separately)
- Perfect showcase for vintage style bulbs including Progress Lighting P7825-01
- The sconces are open on the top and bottom, providing character and visual appeal to the form
- In addition to bath areas, sconces are suitable for hall & foyers to add ambient lighting
- Versatile lighting fixture that complements vintage electric, urban industrial, rustic farmhouse and modern farmhouse interiors.

Category: Bath & Vanity

Finish: Stainless Steel (plated)

Construction: Steel construction

Glass/Shade: Clear Glass

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 30" W., 4.5" ht., 0.75" depth	6" of wire supplied 120 V	Quantity: Four 60w max. Medium Base E26 base	cCSAus Damp location listed 1 year limited warranty