

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300143-009

Nealy

The Nealy Collection four-light bath & vanity offers classic charm with an edge of modern luxury. Curving details are complemented by luxurious opal etched glass shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite detailing and completed with K9 glass and brass-tone accents.

- Etched white glass shades provide a rich glow over the bathroom vanity
- A curving Graphite accent anchored by brass knobs adds a jewel-like flourish to the four-light bath fixture
- Can be mounted up or down to customize a bathroom space
- With its jewelry-like styling, it's well-suited for Modern and Luxe interiors
- Classic Brushed Nickel Finish frame with Graphite detailing
- Measures 30in W x 9in ht.
- Uses four 100-watt max. medium base bulbs or LED equivalent (sold separately)
- UL Safety listed for use in damp locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel Construction

Glass/Shade: Etched White glass Shades



Diameter: 30"
Height: 9"
Depth: 6"
H/CTR: 6-3/8" (glass facing up)

Glass

Width: 4-1/8"

Height: 5-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting swivel mounting bracket for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 9" W., 5" ht., 1.25" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Four 100w max. Medium Base E26 base porcelain sockets	cULus Damp location listed 1 year warranty