

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P300154-104

Adley

Create a haven for relaxation and revival with the Adley one-light bath. This fixture features a Polished Nickel, curved backplate attached to a simple, clear glass shade. The modern piece is perfect for adding ambient light to bathroom and vanity settings in traditional and transitional interiors.

- Perfect for adding ambient lighting to bathroom and vanity settings
- Backplate has graceful, beveled detailing and is attached to a simple bar holding the glass-shaded light
- Finished in sleek Polished Nickel
- Mount on a wall on either side of a mirror to eliminate shadows on the face when getting ready for the day or for a night out
- A sophisticated choice for New Traditional and Transitional settings
- Can be displayed individually or in groups of two or more
- Can be mounted facing up or down
- Measures 4-1/2 in width X 7-3/4 in height, extends 6 in, H/CTR 3-7/8 in
- Uses one 60-watt max medium base bulb, or LED equivalent, that is sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Bath & Vanity

Finish: Polished Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear Glass Cylindrical



Width: 4-1/2"
Height: 7-3/4"
Depth: 6"
H/CTR: 3-7/8" (glass facing up)

Glass
Width: 3-7/8"
Length: 3-7/8"
Height: 5-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting plate for outlet box included</p> <p>Fixture can be installed with glass facing up or down</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>4.5" W., 7.75" ht., 0.8125" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>One 60w max. Medium Base</p> <p>E26 base Porcelain socket</p>	<p>UL/CUL Damp location listed</p> <p>1 year warranty</p>