

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300159-009

Clifton Heights

Distinctive chiseled features and clean lines are key features within the Clifton Heights collection. Inspired by an updated interpretation of Craftsman styling, careful attention to the details delivers a dramatic accent. A Brushed Nickel finish complements elegant etched square glass shades. The Clifton Heights collection enhances a variety of home styles including Farmhouse, Craftsman and Transitional decor. Two-Light bath & vanity fixture.

- Distinctive forms and clean lines are key features within the Clifton Heights collection
- Inspired by Craftsman styling, special attention to decorative details can be appreciated in each fixture
- Elegant etched glass shades
- 2-light wall bracket for bathrooms, powder rooms and hallways
- Uses 2, 100-watt max. medium base bulbs including LED equivalent (sold separately)
- Ideal for Farmhouse and Transitional bathroom spaces
- Mount on wall in bath and vanity settings to enhance a spa-like atmosphere
- Measures 14 1/4" W x 8 3/8" H
- Damp location listed
- Shop the complete Clifton Heights collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor



Width: 14-1/4"
Height: 8-3/8"
Depth: 7-1/8"
H/CTR: 5-3/4" (glass facing up)

Height: 6-1/2"

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass/Shade: Etched Glass Shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 7.25" W., 5.25" ht., 1" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 100w max. Medium Base E26 base Porcelain sockets	cULus Damp location listed 1-year limited warranty