

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300159-31M Clifton Heights

Clifton Heights Collection Two-Light Modern Farmhouse Matte Black Etched Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Glass Square/Rectangular



Width: 14-1/4 in
Extends: 7-1/8 in
Height: 8-3/8 in
H/CTR: 5-3/4 in (glass facing up)

Etched Glass Square/Rectangular
Width: 5-1/2 in
Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) sockets	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.18" W., 5.25" ht., 1" depth		Fully dimmable with dimmable bulbs.	