

Project:		
Fixture Type:		
Location:		
Contact:		



P300160-31M

Clifton Heights

Clifton Heights Collection Three-Light Modern Farmhouse Matte Black Etched Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: Etched Glass Square/Rectangular

Width: 23 in Extends: 7-1/8 in Height: 8-3/8 in

H/CTR: 5-3/4 in (glass facing up)

Etched Glass Square/Rectangular

Width: 5-1/2 in Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) sockets	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC Lamp Type A19 1-year Limited Warranty		1-year Limited Warranty
Fixture can be installed with glass facing up or down	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 5.5" W., 7.18" ht., 1" depth	Fully dimmable with dimmable bulbs.		