

Parallel LED

 Wall Mounted • Damp Location Listed **PROGRESS LED**

Description:

22" Parallel LED bath and vanity fixtures feature a tubular opal glass diffuser paired with a simple, modern oval metal canopy. An integrated LED source provides a variety of energy and cost savings benefits. Suitable for residential and commercial applications, and can be installed vertically or horizontally. Architectural Bronze finish.

Specifications:

- Etched White glass Cylindrical
- A cylindrical design pairs with an oval back plate to create a harmonious design
- 22" linear 35-watt LED bath fixture
- Etched white glass
- Architectural Bronze finish
- Integrated LED source provides a variety of energy and cost savings benefits for the homeowner
- Measures 4 3/4" W x 22 3/8" H
- 2166 lumens 60 lumens/watt (delivered)
- Warm white 3000K lighting color and 90+CRI
- Can be mounted on the wall vertically or horizontally
- Modern style and continuous illumination are ideal for a variety of bath and vanity settings - including Mid-Century and Luxe
- Steel construction
- ADA compliant
- Dimmable with most Triac or ELV type dimmers
- California Title 24 compliant
- Damp location listed
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 7 in W., 4.75 in ht., 0.625 in depth
- Mounting plate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	35 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,166/60.2 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016


P300183-129-30



Dimensions:

Width: 4-3/4 in
 Height: 22-3/8 in
 Depth: 2-3/4 in
 H/CTR: 2-3/8 in

Etched White glass Cylindrical
 Width: 1-15/16 in
 Height: 1-15/16 in



P300183-129-30

Dimming Notes:

P300183-129-30 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron - NTELV-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.