

Project:

Fixture Type:

Location:

Contact:



P300191-009 Axle

Axle Collection 3-Light Brushed Nickel Vintage Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Length: 24 in Extends: 7 in Height: 6-3/4 in

H/CTR: 3.69 in (facing up)

	H/CTR: 3.69 in (facing up)		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting plate for outlet box included Fixture can be installed with glass facing up or down Canopy covers a standard 4" recessed outlet box: 6.125" W., 0.875" ht., 6.125" depth	6 inches of wire supplied 120 V	Quantity: three 60 W max. E26 base Porcelain Socket	cULus Damp Location Listed 1-year Limited Warranty