

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P300201-078

## Rigsby

The use of mixed media highlights a variety of elegant details are featured in the Rigsby Collection's One-light wall bracket. A hint of faux marble appears in the horizontal cross bar, while Vintage Gold and Chrome accents create a dual toned finish. Decorated white gloss hardback shade lined with burnished gold foil complete the fixture.

- A hint of faux marble appears with the chrome metal arm.
- A gold-lined white-gloss shade gives this one-light wall bracket a burnished glow from within
- The brass, chrome and Carrera-like finishes evoke high-end kitchen styling, an ideal complement to similar finishes in a kitchen, breakfast room or bathroom
- Its contemporary restraint and mixed metals make this fixture suitable for Modern and Luxe interiors
- Sensuous Vintage Gold finish with Polished Chrome accents
- Measures 6in W x 13-1/4in ht. x 9-5/8in D, height to center 7-1/2in
- Uses one, 60-watt max. medium base bulb including LED equivalent (sold separately)
- UL Safety listed for use in damp locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



**Diameter: 6"**  
**Height: 13-1/4"**  
**Depth: 9-5/8"**  
**H/CTR: 7-1/2"**

Glass

Width: 6"

Height: 5"

**Category:** Wall Bracket

**Finish:** Vintage Gold (painted)

**Construction:** Steel Construction

**Glass/Shade:** White with Brush Gold Linen paper Shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Back plate covers a standard 4" octagonal recessed outlet box  5" W., 0.75" ht., 5" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  One 60w max. Medium Base  E26 base porcelain socket	cULus Damp location listed  1 year warranty