

Project:		
Fixture Type:		
Location:		
Contact		



P300203-009

Bramlett

Bramlett Collection Four-Light Bath & Vanity

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Graphite Metal Shade

Width: 33-3/8 in Height: 8-1/4 in Depth: 7-1/8 in

H/CTR: 6 in (glass facing up)

Graphite Metal Shade Width: 6-1/16 in Height: 5-13/16 in

		· · · · · · · · · · · · · · · · · · ·		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Wall mounted	Prewired	(4) Medium Base (E26) socket	cULus Damp Location Listed	
swivel mounting strap	6 inches of wire supplied	Lamp Type A19	1-year Limited Warranty	
Fixture can be installed with glass facing up or down	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket		
back plate covers a standard 4" recessed outlet box: 9" W., 4.5" ht., 1" depth		Fully dimmable with dimmable bulbs.		