

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P300203-015 Bramlett

Bramlett Collection Four-Light Bath & Vanity

**Category:** Bath & Vanity  
**Finish:** Polished Chrome (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** White Metal Shade

Width: 33-3/8 in  
Height: 8-1/4 in  
Depth: 7-1/8 in  
H/CTR: 6 in (glass facing up)

White Metal Shade  
Width: 6-1/16 in  
Height: 5-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted swivel mounting strap	Prewired 6 inches of wire supplied	(4) Medium Base (E26) socket Lamp Type A19	cULus Damp Location Listed 1-year Limited Warranty
Fixture can be installed with glass facing up or down back plate covers a standard 4" recessed outlet box: 9" W., 4.5" ht., 1" depth	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket Fully dimmable with dimmable bulbs.	