


Project:
Fixture Type:
Location:







P300215-143

Caisson

Contact:

Infuse your home with the subtle industrial flair of this wall bracket. Inspired by the outstanding architecture of suspension bridges, the light fixture features a fabric cord that attaches to a beautiful graphite light base, smooth round bar, and rectangular backplate. A clear glass shade with a rolled rim at the bottom adds an extra touch of artisan inspiration.

- Infuse your home with the subtle industrial flair of this wall bracket.
- A clear glass shade with a rolled rim at the bottom adds an extra touch of artisan inspiration.
- Inspired by the outstanding architecture of suspension bridges, the light fixture features a
 fabric cord that attaches to a beautiful graphite light base, smooth round bar, and rectangular backplate.
- Ideal for any hallway, foyer, bathroom, sitting room, living room, or stairway.
- Perfect for transitional, modern, or contemporary settings.
- · Measures 7-7/8-inch width by 14-3/4-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Wall Brackets Finish: Graphite (Painted) Construction: Steel Construction Glass/Shade: Clear glass Globe Shade Width: 7-7/8 in Height: 14-3/4 in Depth: 10 in H/CTR: 11-1/4 in

Clear glass Globe Shade

Width: 7 in Height: 9-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 60 W max. Medium Base or	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Back Plate covers a standard 4" recessed outlet box: 4.5" W., 7" ht., 0.75" depth			