

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300219-009

Tobin

A modern take on a classic object, Tobin's inspiration comes from the timeless mid-century forms. The tubular arms of the two-light bath extend outward and are made to form a gentle curve that showcase etched white glass shades and finished in Brushed Nickel. The Tobin collection is ideal for those who appreciate Modern design styles.

- Etched white glass shades punctuate curved tubular fittings that take the edge off these modern bath and vanity fixtures
- The two-light bath can be mounted up or down to customize the look and add to a bathroom's spa-like atmosphere
- Mount on either side of the mirror to eliminate shadows on face when getting ready in the morning
- The sculptural metal and cylindrical glass shades make Tobin ideal for Modern settings
- Sleek Brushed Nickel finish
- Measures 15-1/4in W x 7-7/8in ht.
- Uses two 100-watt max. medium base bulbs or LED equivalent (sold separately)
- UL Safety listed for use in damp locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Width: 15-1/4"
Height: 7-7/8"
Depth: 7-5/8"

Glass
Width: 5"
Height: 5-1/4"

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel Construction

Glass/Shade: Etched White Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Fixture can be installed with glass facing up or down covers a standard 4" octagonal recessed outlet box 7" W., 4.5" ht., 0.75" depth	6" of wire supplied 120 V	Quantity: Two 100w max. Medium Base E26 base porcelain sockets	cULus Damp location listed 1 year warranty