

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300227-143

Rushton

Implement a gaze-grabbing, historical motif with the Rushton two-light bath. A pair of exposed bulbs nestle inside two clear glass shades, stylishly hanging from antique-style sockets. A Graphite-finished rectangular backplate supports two mechanical pulley wheels and Antique Brass tube arms that add a vintage charm ideal for bath vanity or wall sconce in any industrial or farmhouse setting.

- Perfect as a bath vanity above a mirror or as a wall sconce throughout the home wherever a vintage touch is desired
- Antique styling is ideal for industrial and farmhouse settings
- Two-light bath vanity offers a vintage charm that preserves a sense of history
- Industrial pulley wheel detailing with faux metal cord is offset by a simple, rectangular backplate
- Mixed-metal finish of Graphite accented with an Antique Brass tube arm
- Measures 16 in width X 9-1/2 in height, Extends 6 in, H/CTR 7 in
- Uses two 60-watt max medium base bulbs, or LED equivalent, that are sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Bath & Vanity

Finish: Graphite (Painted)

Construction: Steel Construction

Glass/Shade: Clear Glass Bell



Width: 16"
Height: 9-1/2"
Depth: 6"
H/CTR: 7" (glass facing up)

Width: 4-1/2"
Length: 4-1/2"
Height: 5-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting plate for outlet box included Fixture can be installed with glass facing up or down Back Plate covers a standard 4" octagonal recessed outlet box 16" W., 5" ht., 0.75" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 60w max. Medium Base E26 base Porcelain sockets	cULus Damp location listed 1 year warranty