

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P300228-009

## Rushton

The gorgeous, versatile Rushton three-light bath will feel at home illuminating a bathroom or wall in any industrial and farmhouse setting. A terrific trio of exposed bulbs shine from inside the classic cover of clear glass shades anchored by antique-style sockets. Each bulb dangles from a Black tube arm that stylishly wraps around a mechanical pulley wheel attached to a rectangular, Brushed Nickel backplate for an added pinch of historical elegance.

- Perfect as a bath vanity above a mirror or as a wall sconce throughout the home wherever a vintage touch is desired
- Antique styling is ideal for industrial and farmhouse settings
- Three-light bath vanity offers a vintage charm that preserves a sense of history
- Industrial pulley wheel detailing with faux metal cord is offset by a simple, rectangular backplate
- Mixed-metal finish of Brushed Nickel accented with a Black tubed arm
- Measures 24 in width X 9-1/2 in height, Extends 6 in, H/CTR 7 in
- Uses three 60-watt max medium base bulbs, or LED equivalent, that are sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

**Category:** Bath & Vanity

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Clear Glass Bell



**Width:** 24"  
**Height:** 9-1/2"  
**Depth:** 6"  
**H/CTR:** 7" (glass facing up)

**Width:** 4-1/2"  
**Length:** 4-1/2"  
**Height:** 5-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting plate for outlet box included  Fixture can be installed with glass facing up or down  Back Plate covers a standard 4" octagonal recessed outlet box  24" W., 5" ht., 0.75" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  Three 60w max. Medium Base  E26 base Porcelain sockets	cULus Damp location listed  1 year warranty