

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P300231-143

## Briarwood

With a nod to its farmhouse roots, the Briarwood three-light bath offers a triad clear glass shades attached to a Graphite-finished backplate. The X-brace design takes center stage atop a painted light, white-washed, faux wood, rectangular shape, giving the fixture a back country feels making it a suitable choice for bathrooms and hallways in rustic and farmhouse settings.

- Perfect for installing above a bathroom mirror or wherever focused light is desired
- Three-light bath vanity features a classic X-brace pattern as seen on barn or farmhouse doors and gates
- X-brace rests on top of a faux-painted, woodgrain rectangle
- Ideal for rustic and farmhouse setting with its foundation of faux wood metal elements and metal detailing
- Finished in a light, white-washed finish paired with Graphite details
- Measures 24-3/4 in width X 8-1/4 in height, Extends 6-1/2 in, H/CTR 5-7/8 in
- Uses three 60-watt max medium base bulbs, or the LED equivalents, that are sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

**Category:** Bath & Vanity

**Finish:** Graphite (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear Glass Cylindrical



**Width:** 24-3/4"  
**Height:** 8-1/4"  
**Depth:** 6-1/2"  
**H/CTR:** 5-7/8" (glass facing up)

**Width:** 4-3/4"  
**Length:** 4-3/4"  
**Height:** 6"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting plate for outlet box included  Fixture can be installed with glass facing up or down  Back Plate covers a standard 4" octagonal recessed outlet box  24" W., 4.75" ht., 1" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  Three 60w max. Medium Base  E26 base Porcelain sockets	UL/CUL Damp location listed  1 year warranty