

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



Incandescent

# P300232-143

## Briarwood

The homespun, X-brace design of the Briarwood four-light bath creates a rustic scene against a rectangular, faux wood and Graphite-finished backplate. A quartet of clear, glass shades are supported by curved, sleek arms. The rustic design makes the fixture an excellent choice for bathroom mirrors and hallways in Rustic and Farmhouse settings.

- Perfect for installing above a bathroom mirror or wherever focused light is desired
- Four-light bath vanity features a classic X-brace pattern as seen on barn or farmhouse doors and gates
- X-brace rests on top of a faux-painted woodgrain rectangle
- Ideal for rustic and farmhouse settings with its foundation of faux wood metal elements and metal detailing
- Finished in a light, white-washed finish paired with Graphite details
- Measures 34-3/4 in width X 8-1/4 in height, Extends 6-1/2 in, H/CTR 5-7/8 in
- Uses four 60-watt max medium base bulbs, or the LED equivalents, that are sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

**Width: 34-3/4"**  
**Height: 8-1/4"**  
**Depth: 6-1/2"**  
**H/CTR: 5-7/8" (glass facing up)**

Width: 4-3/4"  
Length: 4-3/4"  
Height: 6"

**Category:** Bath & Vanity

**Finish:** Graphite (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear Glass Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting plate for outlet box included  Fixture can be installed with glass facing up or down  Back Plate covers a standard 4" octagonal recessed outlet box  34" W., 4.75" ht., 1" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  Four 60w max. Medium Base  E26 base Porcelain sockets	UL/CUL Damp location listed  1 year warranty