

| DATE: | TYPE: | |
|----------|-------|--|
| NAME: | | |
| PROJECT: | | |



P300234-009

Classic

Adopt a never-out-of-style design with the impeccably crafted Classic onelight bath. A distinguished, Black circular backplate supports a graceful curved arm holding a bell-shaped, etched glass shade. This flawless fixture is perfect for chasing away the shadows around a bathroom mirror, in a dining room or in other living areas craving task light.

- Perfect for installing in a bathroom on either side of a mirror, in a dining room, or in other living areas where task light is desired
- Two-light bath vanity with simple, curved arms extending from a rounded backplate
- Bell-shaped, etched-glass shades for a soft glow
- A blend of contemporary and traditional styling makes the fixture ideal for transitional settings
- Finished in subtly reflective Brushed Nickel
- Can be mounted facing up or down
- Measures 13 in width X 7-7/8 in height, extends 7 in, H/CTR 3 in
- Uses two 100-watt max medium base bulbs, or the LED equivalents, that are sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Bell

| Width: 13" |
|----------------|
| Height: 7-7/8" |
| Depth: 7" |

H/CTR: 3" (glass facing up)

Glass Width: 5" Length: 5" Height: 5-5/16"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|------------------------------|--|----------------------------|
| Wall mounted | Pre-wired | Quantity: | cULus Damp location listed |
| Mounting PLATE for outlet box included Fixture can be installed with glass facing up or down | 6" of wire supplied 120 V | Two 100w max. Medium Base E26 base Porcelain sockets | 1 year warranty |
| Back Plate covers a standard 4" octagonal recessed outlet box 12" W., 4.625" ht., 0.75" depth | | | |