

Project:			
Fixture Type:			
Location:			
Contact:			

P300254-151

Bowman

Beautiful lighting will appeal to both your classic taste and your artistic spirit with this bath light. Wandering eyes will focus on clear chiseled glass shades as they offer an air of refinery. Handsome cottage white light bases are supported by dainty curved arms to complete the elegant design.

- · Wandering eyes will focus on clear chiseled glass shades as they offer an air of refinery.
- Handsome cottage white light bases are supported by dainty curved arms to complete the elegant design.
- Beautiful lighting will appeal to both your classic taste and your artistic spirit with this bath light.
- · Ideal for any bathroom.
- · Perfect for transitional, rustic, farmhouse, or coastal settings.
- · Measures 16-3/8-inch width by 7-3/4-inch height.
- Uses two medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Cottage White (Painted) Construction: Steel Construction

Glass/Shade: Clear Chiseled glass bell shaped shade



Width: 16-3/8 in Height: 7-3/4 in Depth: 7-3/8 in

H/CTR: 3-1/4 in (glass facing up)

Clear Chiseled glass bell shaped shade

Width: 4-13/16 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Two 60 W max. Medium Base or	CULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Sex meladed	120 V	E26 base Porcelain sockets	
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 8" W., 5" ht., 0.8125" depth			