

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300256-151
Bowman

Bowman Collection Cottage White Four-Light Bath

Category: Bath & Vanity
Finish: Cottage White (Painted)
Construction: Steel Construction
Glass/Shade: Clear Chiseled Glass Bell Shaped Shade

Width: 33-5/8 in
Height: 7-3/4 in
Depth: 7-3/8 in
H/CTR: 3-1/4 in (glass facing up)

Clear Chiseled Glass Bell Shaped Shade
Width: 4-13/16 in
Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: four 60 W max. A-19 or LED equivalent	cULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	E26 base Porcelain sockets	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V		
Canopy covers a standard 4" recessed outlet box: 8" W., 5" ht., 0.8125" depth			