

Project:

Fixture Type:

Location:

Contact:

## P300257-031 Lassiter

Manifest a swoon-worthy lighting experience with the stunning blend of modern and traditional styles in this one-of-a-kind light fixture. Square tubing with clean, sharp angles demand your attention and appreciation. A beautiful black finish coats a handsome rectangular backplate. Striking vintage light sockets boast their bold yet simple demeanors within the safety of sophisticated clear glass shades.

- Striking vintage light sockets boast their bold yet simple demeanors within the safety of sophisticated clear glass shades.
- · A beautiful black finish coats a handsome rectangular backplate.
- · A stunning blend of modern and traditional styles in a one-of-a-kind fixture.
- · Ideal for any bathroom.
- Perfect for modern, new traditional, or contemporary settings.
- · Measures 16-inch width by 8-inch height.
- Uses two medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade,



Width: 16 in Height: 8 in Depth: 5-1/2 in

H/CTR: 5-1/2 in (glass facing up)

Clear glass Cylindrical Shade

Width: 4 in Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Two 60 W max. Medium Base or	CULus Damp Location Listed
Mounting plate for outlet box included	6" of wire supplied	LED equivalent	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4" recessed outlet box: 8" W., 4.875" ht., 0.875" depth			