PROGRESS LIGHTING[™]

Project:		
Fixture Type:		

Location:

Contact:

P300259-009 Lassiter

Manifest a swoon-worthy lighting experience with the stunning blend of modern and traditional styles in this one-of-a-kind bath light. Square tubing with clean, sharp angles demand your attention and appreciation. A beautiful brushed nickel finish coats a handsome rectangular backplate. Striking vintage light sockets boast their bold yet simple demeanors within the safety of sophisticated clear glass shades.

- Striking vintage light sockets boast their bold yet simple demeanors within the safety of sophisticated clear glass shades.
- A beautiful brushed nickel finish coats a handsome rectangular backplate.
- Square tubing with clean, sharp angles demand your attention and appreciation.
- Ideal for any bathroom.
- Perfect for modern, new traditional, or contemporary settings.
- Measures 34-inch width by 8-inch height.
- Uses four medium base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear glass Cylindrical Shade,



Width: 34 in Height: 8 in Depth: 8-1/8 in H/CTR: 5-5/8 in (glass facing up)

Clear glass Cylindrical Shade Width: 4 in Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Four 60 W max. Medium Base or	CULus Damp Location Listed
Mounting plate for outlet box included	6" of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
Fixture can be installed with glass facing up or down			

Canopy covers a standard 4" recessed outlet box: 8" W., 4.875" ht., 0.875" depth