

Project:			
Fixture Type:			
Location:			
Contact:			

P300261-009

Durrell

This versatile bath light will find a home in a variety of settings in need of generous illumination. A crisp clear glass shade rests on top of a vintage-style light base. A smooth, curved bar supports the light base and attaches to a brushed nickel oval backplate.

- · A crisp clear glass shade rests on top of a vintage-style light base.
- A smooth, curved bar supports the light base and attaches to a brushed nickel oval backplate.
- This versatile bath light will find a home in a variety of settings in need of generous illumination.
- · Ideal for any bathroom.
- Perfect for rustic, farmhouse, or coastal settings.
- Measures 4-5/8-inch width by 7-7/8-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- $\boldsymbol{\cdot}$ Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Clear glass bell shaped shade



Width: 4-5/8 in Height: 7-7/8 in Depth: 6-1/4 in

H/CTR: 4 in (glass facing up)

Clear glass bell shaped shade

Width: 4-9/16 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 60 W max. Medium Base or	CULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.875" ht., 0.875" depth			