PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P300261-031 Durrell

This versatile bath light will find a home in a variety of settings in need of generous illumination. A crisp clear glass shade rests on top of a vintage-style light base. A smooth, curved bar supports the light base and attaches to a black oval backplate.

- A crisp clear glass shade rests on top of a vintage-style light base.
- A smooth, curved bar supports the light base and attaches to a black oval backplate.
- This versatile bath light will find a home in a variety of settings in need of generous illumination.
- Ideal for any bathroom.
- · Perfect for rustic, farmhouse, or coastal settings.
- Measures 4-5/8-inch width by 7-7/8-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear glass bell shaped shade



Width: 4-5/8 in Height: 7-7/8 in Depth: 6-1/4 in H/CTR: 4 in (glass facing up)

Clear glass bell shaped shade Width: 4-9/16 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 60 W max. Medium Base or	CULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Fixture can be installed with glass	120 V	E26 base Porcelain socket	

Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.875" ht., 0.875" depth

facing up or down