PROGRESS LIGHTING[™]

Project:

Fixture Type:

Location:

Contact:

P300263-031 Durrell

This versatile bath light will find a home in a variety of settings in need of generous illumination. Crisp clear glass shades rest on top of vintage-style light bases. Smooth, curved arms support the light bases and attach to a black backplate.

- Crisp clear glass shades rest on top of vintage-style light bases.
- Smooth, curved arms support the light bases and attach to a black backplate.
- This versatile bath light will find a home in a variety of settings in need of generous illumination.
- Ideal for any bathroom.
- Perfect for rustic, farmhouse, or coastal settings.
- Measures 22-3/8-inch width by 7-7/8-inch height.
- Uses three medium base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear glass bell shaped shade



Width: 22-3/8 in Height: 7-7/8 in Depth: 6-1/4 in H/CTR: 5-1/4 in (glass facing up)

Clear glass bell shaped shade Width: 4-9/16 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Three 60 W max. Medium Base or	CULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
Fixture can be installed with glass facing up or down			

Canopy covers a standard 4" recessed outlet box: 6.875" W., 4.5" ht., 0.875" depth