

Project:		
Fixture Type:		
Location:		
Contact:		



P300264-009

Durrell

This versatile bath light will find a home in a variety of settings in need of generous illumination. Crisp clear glass shades rest on top of vintage-style light bases. Smooth, curved arms support the light bases and attach to a brushed nickel backplate.

- · Crisp clear glass shades rest on top of vintage-style light bases.
- · Smooth, curved arms support the light bases and attach to a brushed nickel backplate.
- This versatile bath light will find a home in a variety of settings in need of generous illumination.
- · Ideal for any bathroom.
- · Perfect for rustic, farmhouse, or coastal settings.
- · Measures 31-1/4-inch width by 7-7/8-inch height.
- Uses four medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Clear glass bell shaped shade

Width: 31-1/4 in Height: 7-7/8 in Depth: 6-1/4 in

H/CTR: 5-1/4 in (glass facing up)

Clear glass bell shaped shade

Width: 4-9/16 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Four 60 W max. Medium Base or	CULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 6.875" W., 4.5" ht., 0.875" depth			