

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300264-031

Durrell

This versatile bath light will find a home in a variety of settings in need of generous illumination. Crisp clear glass shades rest on top of vintage-style light bases. Smooth, curved arms support the light bases and attach to a black backplate.

- Crisp clear glass shades rest on top of vintage-style light bases.
- Smooth, curved arms support the light bases and attach to a matte black backplate.
- This versatile bath light will find a home in a variety of settings in need of generous illumination.
- Ideal for any bathroom.
- Perfect for rustic, farmhouse, or coastal settings.
- Measures 31-1/4-inch width by 7-7/8-inch height.
- Uses four medium base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Width: 31-1/4 in
Height: 7-7/8 in
Depth: 6-1/4 in
H/CTR: 5-1/4 in (glass facing up)

Clear glass bell shaped shade
Width: 4-9/16 in
Height: 6 in

Category: Bath & Vanity

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear glass bell shaped shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Four 60 W max. Medium Base or LED equivalent	CULus Damp Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	E26 base Porcelain sockets	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V		
Canopy covers a standard 4" recessed outlet box: 6.875" W., 4.5" ht., 0.875" depth			