

Project:	
Fixture Type:	
_ocation:	
Contact	

## P300266-135

## **Dwyer**

Incorporate a vintage feel with a dash of industrial personality with this three-light bath. An attention-grabbing, clear ribbed glass takes center stage in the design to create a gaslight glow when the fixture is illuminated. A simple, metal frame coated in a sleek stainless steel finish encases the ribbed glass to emphasize the light fixture's chic industrial edge.

- An attention-grabbing, clear ribbed glass takes center stage in the design to create a gaslight glow when the fixture is illuminated.
- A simple metal frame coated in a sleek stainless steel finish encases the ribbed glass to emphasize the light fixture's chic industrial edge.
- Incorporate a vintage feel with a dash of industrial personality with this three-light bath.
- · Ideal for any bathroom.
- · Perfect for mid-century, modern, farmhouse, or bohemian settings.
- · Measures 22-inch width by 5-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity

Finish: Stainless Steel (Clear Coat)

Construction: Steel and Stainless Steel Construction

Glass/Shade: Clear Ribbed glass Panel, Clear Ribbed Glass Panel

Width: 22 in Height: 5 in Depth: 4-1/2 in H/CTR: 2-1/4 in

Clear Ribbed glass Panel

Width: 21-3/4 in Height: 4-1/4 in

Clear Ribbed Glass Panel

Width: 3-1/4 in Height: 4-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal or vertical mounted	Prewired	Quantity: Three 60 W max. Candelabra	CULus Damp Location Listed
Mounting backplate for outlet	6 inches of wire supplied	Base (G16.5) or LED equivalent	1-year Limited Warranty
box included	120 V	E12 base Phenolic sockets	
Back Plate covers a standard 4" recessed outlet box: 22" W., 4.5" ht., 1" depth			