

Project:			
Fixture Type:			
Location:			
Contact			

## P300268-009

## **Fawcett**

Open the door to a world of modern elegance with the clean and crisp Fawcett Collection Brushed Nickel One-Light Bath. A signature, clear faceted glass shade provides a calming and relaxing lighting experience. The shade is held in place by a handsome backplate coated in a brushed nickel finish.

- A signature, clear faceted glass shade provides a calming and relaxing lighting experience.
- The shade is held in place by a handsome backplate coated in a brushed nickel finish.
- · Open the door to a world of modern elegance with this clean and crisp bath light.
- · Ideal for any bathroom.
- · Perfect for urban industrial or coastal settings.
- · Measures 4-1/2-inch width by 7-3/4-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Clear Patterned glass Cylindrical Shade



Width: 4-1/2 in Height: 7-3/4 in Depth: 5-7/8 in

H/CTR: 4-1/2 in (glass facing up)

Clear Patterned glass Cylindrical Shade

Width: 4 in Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.5" ht., 0.75" depth			