

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300269-009

Fawcett

Open the door to a world of modern elegance with the clean and crisp Fawcett Collection Brushed Nickel Two-Light Bath. Signature clear patterned glass shades provide a calming and relaxing lighting experience. Each shade is held in place by gentle backplates coated in a beautiful brushed nickel finish.

- Signature clear patterned glass shades provide a calming and relaxing lighting experience.
- Each shade is held in place by gentle backplates coated in a beautiful brushed nickel finish.
- Open the door to a world of modern elegance with this clean and crisp bath light.
- Ideal for any bathroom.
- Perfect for urban industrial or coastal settings.
- Measures 13-1/8-inch width by 7-3/4-inch height.
- Uses two medium base bulbs that are sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear Patterned glass Cylindrical Shade



Width: 13-1/8 in
Height: 7-3/4 in
Depth: 5-7/8 in
H/CTR: 5-1/2 in (glass facing up)

Clear Patterned glass Cylindrical Shade
Width: 4 in
Height: 5-3/4 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---------------------------|---|----------------------------|
| Wall mounted | Prewired | Quantity: Two 100 W max. Medium Base or LED equivalent | CULus Damp Location Listed |
| Mounting plate for outlet box included | 6 inches of wire supplied | E26 base Porcelain sockets | 1-year Limited Warranty |
| Fixture can be installed with glass facing up or down | 120 V | | |
| Canopy covers a standard 4" recessed outlet box: 6.5" W., 4.5" ht., 0.75" depth | | | |