PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P300271-009 Fawcett

Open the door to a world of modern elegance with the clean and crisp Fawcett Collection Brushed Nickel Four-Light Bath. Signature clear patterned glass shades provide a calming and relaxing lighting experience. Each shade is held in place by gentle backplates coated in a beautiful brushed nickel finish.

- Signature clear patterned glass shades provide a calming and relaxing lighting experience.
- Each shade is held in place by gentle backplates coated in a beautiful brushed nickel finish.
- Open the door to a world of modern elegance with this clean and crisp bath light.
- Ideal for any bathroom.
- Perfect for urban industrial or coastal settings.
- Measures 31-1/8-inch width by 7-3/4-inch height.
- Uses four medium base bulbs that are sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Patterned glass Cylindrical Shade



Width: 31-1/8 in Height: 7-3/4 in Depth: 5-7/8 in H/CTR: 5-1/2 in (glass facing up)

Clear Patterned glass Cylindrical Shade Width: 4 in Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Four 100 W max. Medium Base or	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	E26 base Porcelain sockets	

Canopy covers a standard 4" recessed outlet box: 6.5" W., 4.5" ht., 0.75" depth