

Project:			
Fixture Type:			
Location:			
Contact:			

## P300272-031 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this one-light bath from the Winslett Collection. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a beautiful black finish. A lightly seeded glass shade rests in a shiny pedestal light base that adds an unexpected, but welcomed dash of modern personality to this clean, traditional design.

- A lightly seeded glass shade rests in a shiny pedestal light base that adds an unexpected, but welcome dash of modern personality to this clean, traditional design.
- Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines coated in a beautiful black finish.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftmanship of this one-light bath.
- · Ideal for any bathroom.
- · Perfect for transitional, rustic, farmhouse, and coastal settings.
- · Measures 4-3/4-inch width by 9-1/2-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction

Glass/Shade: Clear Seeded glass Cylindrical Shade



Width: 4-3/4 in Height: 9-1/2 in Depth: 6-3/4 in

H/CTR: 4-3/4 in (glass facing up)

Clear Seeded glass Cylindrical Shade

Width: 4-3/4 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Wall mounted	Prewired	Quantity: One 60 W max. Medium Base or	CULus Damp Location Listed	
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty	
	120 V	E26 base Porcelain socket		
Fixture can be installed with glass facing up or down				
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7.125" ht., 0.75" depth				