

Project:			
Fixture Type:			
Location:			
Contact			

## P300277-009 Riley

Incorporate a sleek simplicity and natural beauty with the Riley Collection's Two-Light Brushed Nickel Bath. Clear glass shades offer rejuvenating illumination. The shades rest on a gorgeous brushed nickel frame with polished chrome finials for an overall design that exudes a feeling of tranquility and serenity.

- · Clear glass shades are ready to offer stunning, rejuvenating illumination.
- The shades rest on a gorgeous brushed nickel frame with polished chrome finials.
- Incorporate a sleek simplicity and natural beauty with this bath light.
- · Ideal for any bathroom.
- · Perfect for new traditional or contemporary settings.
- Measures 16-1/8-inch width by 8-1/4-inch height.
- Uses two medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Bath & Vanity **Finish:** Brushed Nickel (Plated) **Construction:** Steel Construction

Glass/Shade: Clear glass Cylindrical Shade



Width: 16-1/8 in Height: 8-1/4 in Depth: 5-1/2 in

H/CTR: 5-3/4 in (glass facing up)

Clear glass Cylindrical Shade

Width: 3-7/8 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Two 60 W max. Medium Base or	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 9" W., 5" ht., 1.125" depth			